







LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECR-12-003555	19APR2012	RS	DD
			A2	REVISED PER ECR-12-016877	20OCT2012	RS	DD
			B	REVISED PER ECR-15-004054	28JUL2015	RS	DD
			C	REVISED PER ECR-15-017995	18DEC2015	RS	DD



- | | | | |
|---|---|---|-----------------|
| △ | MATERIALS AND FINISH:
- HOUSING: LCP, COLOR: NATURAL
- CONTACTS: COPPER ALLOY, FINISH: Sn OVER Ni | B | REVISED PER ECR |
| | | C | REVISED PER ECR |

2. COMPLY WITH DIRECTIVE 2002/95/EC (ROHS).

3. 18-24AWG SOLID OR STRANDED WIRE.
PLEASE REFER TO APPLICATION SPEC 114-13266
FOR RECOMMENDED STRAND COUNT.

18AWG	MAX	INSULATION	OD:	2.20
20AWG	MAX	INSULATION	OD:	1.90
22AWG	MAX	INSULATION	OD:	1.70
24AWG	MAX	INSULATION	OD:	1.45

4. PACKAGE IN TAPE AND REEL PER EIA-481 SPECIFICATION, EXCEPT 1 POSITION CONNECTOR.

5 WIRE SIZE MARKING IN APPROXIMATE LOCATION SHOWN.


6 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

△ 7 COLOR CODE MARKING, STRAIGHT LINE.


⑧ 1 POSITION ASSEMBLY DOES NOT COMPLY WITH EIA 481 SPECIFICATION.

RED	17.70	24 AWG	4	3-2106431-4
	13.70	24 AWG	3	3-2106431-3
	9.70	24 AWG	2	3-2106431-2
	5.70	24 AWG	1	 3-2106431-1
GREEN	17.70	22 AWG	4	2-2106431-4
	13.70	22 AWG	3	2-2106431-3
	9.70	22 AWG	2	2-2106431-2
	5.70	22 AWG	1	 2-2106431-1
BLUE	17.70	20 AWG	4	1-2106431-4
	13.70	20 AWG	3	1-2106431-3
	9.70	20 AWG	2	1-2106431-2
	5.70	20 AWG	1	 1-2106431-1
YELLOW	17.70	18 AWG	4	2106431-4
	13.70	18 AWG	3	2106431-3
	9.70	18 AWG	2	2106431-2
	5.70	18 AWG	1	 2106431-1
COLOR CODE	DIM D	WIRE SIZE	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C DAILY 09DEC2008		TE Connectivity	
DIMENSIONS: mm		CHK J DYER 09DEC2008		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -		ASSEMBLY, IDC SSL CONNECTOR, SMT, PASS THRU	
		PRODUCT SPEC 108-2404		SIZE	
0 PLC ±.5 1 PLC ±0.13 2 PLC ±.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		APPLICATION SPEC 114-13266		CAGE CODE	
MATERIAL		WEIGHT -		DRAWING NO	
				RESTRICTED TO	
		Customer Drawing		SCALE 8.1	
				SHEET 1 OF 3	
				REV C	



3 POSITION
RECOMMENDED PAD LAYOUT
SCALE 8:1



4 POSITION
RECOMMENDED PAD LAYOUT
SCALE 8:1

D

C

B




A

D

C

B

A



SECTION X-X

2106431-2 SHOWN IN POCKET TAPE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C DAILY

CHK
J DYER

APVD
-

PRODUCT SPEC
108-2404

APPLICATION SPEC
114-13266

WEIGHT
-

Customer Drawing

09DEC2008

09DEC2008

-

108-2404

114-13266

-

SCALE 8:1

TE Connectivity

NAME
ASSEMBLY,
IDC SSL CONNECTOR,
SMT, PASS THRU

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2106431

RESTRICTED TO
-

SHEET 1 OF 3

REV C

DIMENSIONS:
mm

0 PLC ±

1 PLC ±0.5

2 PLC ±0.13

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±

±

±

±

±

±

-

MATERIAL
-

material_2