

Han 3EMC-HTE-2 Pegs-M20 w. glued sealing



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 003 1443
Specification	Han 3EMC-HTE-2 Pegs-M20 w. glued sealing
HARTING eCatalogue	https://b2b.harting.com/19620031443

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® EMC
Type of hood/housing	Hood
Description of hood/housing	for Han-Brid® With glued seal

Version

Size	3 A
Version	Top entry
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Hoods/Housings for higher EMC requirements
Pack contents	Please order seal screw separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
-------------------------	---------------



Pushing Performance
Since 1945

Material properties

Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene

Specifications and approvals

Approvals	CE
	DNV GL

Commercial data

Packaging size	10
Net weight	60.27 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140132344
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors