



0512




0512-0-15-XX-12-XX-04-0
Press-fit in .057 mounting hole

2218




2218-0-15-XX-22-XX-10-0
Press-fit in .057 mounting hole

0703




0703-0-15-XX-12-XX-04-0
Press-fit in .057 mounting hole

0574




0574-0-15-XX-12-XX-04-0
Press-fit in .057 mounting hole

0468




0468-0-15-XX-12-XX-04-0
Press-fit in .057 mounting hole

0550




0550-0-15-XX-22-XX-10-0
Solder mount in .052 min. mounting hole

0671




0671-0-15-XX-12-XX-10-0
Solder mount in .063 min. mounting hole

0707




0707-0-15-XX-12-XX-10-0
Solder mount in .051 min. mounting hole

5739



5739-0-18-XX-12-XX-10-0
Surface mount
Also available on 16mm wide carrier tape: 3,000 parts per 13" reel.
Order as: 5739-0-67-XX-12-XX-10-0

8894



8894-0-15-XX-12-XX-10-0
Hex press-fit in .059 plated thru hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: $\pm .005$
DIAMETERS: $\pm .002$
ANGLES: $\pm 2^\circ$

ORDER CODE: XXXX - X - 1X - XX - XX - XX - XX - 0

BASIC PART #
SPECIFY SHELL FINISH:
01 200 μ " TIN/LEAD OVER NICKEL
15 10 μ " GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
02 200 μ " TIN/LEAD OVER NICKEL
14 10 μ " GOLD OVER NICKEL
27 30 μ " GOLD OVER NICKEL

SELECT CONTACT
#12 or #22 CONTACT (DATA ON PAGE 207)