

D-SUB STANDARD

Solder pin – Straight – Stamped contacts






RoHS compliant – CSA listed, File No.: LR 115000-1 – UL listed, File No.: E202784




SOCKET CONNECTOR

9-37 pos.

No. of pos.	A	B	C	D
09	30.80	16.30	25.00	19.20
15	39.20	24.60	33.30	27.70
25	53.10	38.30	47.04	41.10
37	69.40	54.80	63.50	57.30



50 pos.






DESCRIPTION

- Mounting styles:
 - with through-hole, Ø .118" / 3 mm
 - with 4-40 UNC threaded insert
 - with 4-40 UNC threaded rear spacer
 - with 4-40 UNC threaded rear spacer with PCB clip
 - with 4-40 UNC front and threaded rear spacer with PCB clip
- Quality class 3 (other quality classes on request)
- Shell: Steel tin plated




PLUG CONNECTOR

9-37 pos.

No. of pos.	A	B	C	D
09	30.80	16.92	25.00	19.20
15	39.20	25.25	33.30	27.70
25	53.10	38.96	47.04	41.10
37	69.40	55.42	63.50	57.30




50 pos.



D-SUB STANDARD – MOUNTING STYLES

Solder pin – Straight – Stamped contacts

ORDER DATA




SOCKET CONNECTOR

No. of pos.	Mounting style	Part Number
09	Through-hole	DLS 1XS4AD01 X
15	Through-hole	DLS 2XS4AD01 X
25	Through-hole	DLS 3XS4AD01 X
37	Through-hole	DLS 4XS4AD01 X
50	Through-hole	DLS 5XS4AD01 X

PLUG CONNECTOR

No. of pos.	Mounting style	Part Number
09	Through-hole	DLS 1XP4AD01 X
15	Through-hole	DLS 2XP4AD01 X
25	Through-hole	DLS 3XP4AD01 X
37	Through-hole	DLS 4XP4AD01 X
50	Through-hole	DLS 5XP4AD01 X




SOCKET CONNECTOR

No. of pos.	Mounting style 4-40 UNC	Part Number
09	Threaded insert	DLS 1XS4AG06 X
15	Threaded insert	DLS 2XS4AG06 X
25	Threaded insert	DLS 3XS4AG06 X
37	Threaded insert	DLS 4XS4AG06 X
50	Threaded insert	DLS 5XS4AG06 X

PLUG CONNECTOR

No. of pos.	Mounting style 4-40 UNC	Part Number
09	Threaded insert	DLS 1XP4AG06 X
15	Threaded insert	DLS 2XP4AG06 X
25	Threaded insert	DLS 3XP4AG06 X
37	Threaded insert	DLS 4XP4AG06 X
50	Threaded insert	DLS 5XP4AG06 X




SOCKET CONNECTOR

No. of pos.	Mounting style 4-40 UNC	Part Number
09	Threaded rear spacer	DLS 1XS4AA37 X
15	Threaded rear spacer	DLS 2XS4AA37 X
25	Threaded rear spacer	DLS 3XS4AA37 X
37	Threaded rear spacer	DLS 4XS4AA37 X
50	Threaded rear spacer	DLS 5XS4AA37 X

PLUG CONNECTOR

No. of pos.	Mounting style 4-40 UNC	Part Number
09	Threaded rear spacer	DLS 1XP4AA37 X
15	Threaded rear spacer	DLS 2XP4AA37 X
25	Threaded rear spacer	DLS 3XP4AA37 X
37	Threaded rear spacer	DLS 4XP4AA37 X
50	Threaded rear spacer	DLS 5XP4AA37 X




SOCKET CONNECTOR

No. of pos.	Mounting style 4-40 UNC	Part Number
09	Threaded rear spacer PCB clip	DLS 1XS4AA35 X
15	Threaded rear spacer PCB clip	DLS 2XS4AA35 X
25	Threaded rear spacer PCB clip	DLS 3XS4AA35 X
37	Threaded rear spacer PCB clip	DLS 4XS4AA35 X
50	Threaded rear spacer PCB clip	DLS 5XS4AA35 X

PLUG CONNECTOR

No. of pos.	Mounting style 4-40 UNC	Part Number
09	Threaded rear spacer PCB clip	DLS 1XP4AA35 X
15	Threaded rear spacer PCB clip	DLS 2XP4AA35 X
25	Threaded rear spacer PCB clip	DLS 3XP4AA35 X
37	Threaded rear spacer PCB clip	DLS 4XP4AA35 X
50	Threaded rear spacer PCB clip	DLS 5XP4AA35 X



SOCKET CONNECTOR

No. of pos.	Mounting style 4-40 UNC	Part Number
09	Front/Threaded rear spacer PCB clip	DLS 1XS4AA39 X
15	Front/Threaded rear spacer PCB clip	DLS 2XS4AA39 X
25	Front/Threaded rear spacer PCB clip	DLS 3XS4AA39 X
37	Front/Threaded rear spacer PCB clip	DLS 4XS4AA39 X
50	Front/Threaded rear spacer PCB clip	DLS 5XS4AA39 X

PLUG CONNECTOR

No. of pos.	Mounting style 4-40 UNC	Part Number
09	Front/Threaded rear spacer PCB clip	DLS 1XP4AA39 X
15	Front/Threaded rear spacer PCB clip	DLS 2XP4AA39 X
25	Front/Threaded rear spacer PCB clip	DLS 3XP4AA39 X
37	Front/Threaded rear spacer PCB clip	DLS 4XP4AA39 X
50	Front/Threaded rear spacer PCB clip	DLS 5XP4AA39 X

PCB clip for .126"/3.2 ± .004"/0.10 mm hole diameter and .063"/1.6 mm circuit board thickness.