



LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	DWN
			D2	REVISED PER ECR-10-013696	19AUG10	HMR
						APVD
						GJ

- 1
- SPECIFICATIONS:
MAGNET WIRE #18 - #34 AWG,
1.02MM(.040)-0.16MM(.006) DIA COPPER.
OTHER SIZES MAY BE ACCOMMODATED,
CONSULT TYCO ELECTRONICS FOR APPROVAL.
- 2
- POCKET RECOMMENDATION: #1601425
ALTERNATE POCKET #1601421
- 3
- TERMINAL TO APPLIED PER TYCO ELECTRONICS
SPECIFICATION 114-13166 FIGURE 8.
- 4
- TWO(2) TERMINALS SHOWN FOR ILLUSTRATION
PURPOSES ONLY.



-	-	-
-	-	-
-	-	-
UNPLATED	031-093-000	4-1601045-1
UNPLATED	131-094-000	2-1601045-1
UNPLATED	131-093-000	1601045-1
FINISH	REFERENCE PART NUMBER	TE PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: mm [INCHES]	DWN J.WELLER 11JAN2002	Tyco Electronics Corporation Harrisburg, PA 17105-3608
	CHK M.FEHER 11JAN2002	
	APVD K.RANDOLPH 11JAN2002	NAME STANDARD RANGE WIRE TO 2.79 X 0.51 TAB SIAMEZE TERMINAL
	PRODUCT SPEC 108-2085	
MATERIAL BRASS, SPRING HARD	APPLICATION SPEC 3	SIZE A2
	FINISH SEE TABLE	CAGE CODE 00779
CUSTOMER DRAWING		DRAWING NO C=1601045
SCALE 6:1		RESTRICTED TO -
SHEET 1 OF 1		REV D2