






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE PER ECR-19-000700	16JAN2019	JS	DD



- 1 MATERIALS:
HOUSING AND CAP: PBT
DIMMING CONTACTS: COPPER ALLOY
LINE VOLTAGE CONTACTS: COPPER ALLOY
SHORTING CLIP: COPPER ALLOY
GASKET: NBR/PVC BLEND
O-RING: SILICONE RUBBER
MEMBRANE VENT: PTFE
- 2 FINISH:
DIMMING CONTACTS: NICKEL UNDERPLATE ENTIRE
CONTACT 0.127 μ m MIN THICK. SELECTIVE GOLD PLATE CONTACT
MATING AREA (MATING FACE SIDE ONLY) 0.76 μ m MIN THICK.
MATTE TIN PLATE TAB ON BOTH SIDES 0.30 μ m MIN THICK.
LINE VOLTAGE CONTACTS: MATTE TIN PLATE
- 3 MATING INTERFACE PER ANSI C136.41-2013.
- 4 ADHESIVE BACKED GASKET SUPPLIED BUT NOT INSTALLED
5. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
- 6 VENT FEATURES ONLY ON 1-2325661-1






1-2325661-1 SHOWN

VENT	1-2325661-1
NO VENT	2325661-1
NOTES	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 03OCT2017	TE Connectivity			
		CHK MSTOLLER 03OCT2017				
DIMENSIONS:		APVD -	NAME SHORTING BASE ASSEMBLY, LUMAWISE ENDURANCE N			
mm		PRODUCT SPEC 108-32125	SIZE A2			
		APPLICATION SPEC 114-32159	CAGE CODE -			
MATERIAL		WEIGHT -	DRAWING NO C-2325661			
1		2	RESTRICTED TO -			
		CUSTOMER DRAWING	SCALE 1:1			
			SHEET 1 OF 2			
			REV A			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 03OCT2017	TE Connectivity			
DIMENSIONS:		CHK M. STOLLER 03OCT2017				
mm		APVD -	NAME SHORTING BASE ASSEMBLY, LUMAWISE ENDURANCE N			
		PRODUCT SPEC 108-32125	SIZE A2			
		APPLICATION SPEC 114-32159				
MATERIAL		WEIGHT -	CAGE CODE -	DRAWING NO C-2325661	RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE 1:1	SHEET 2 OF 2	REV A