





LOC	DIST	REVISIONS					
AI	-	P	LTR	DESCRIPTION	DATE	OWN	APVD
			C	NEW DRAWING	01DEC2011	SH	KR





NOTES:
Bemerkungen:

¹ INTERFACE SPEC. SEE: BROSE NORM BN 590011-XXX / BN 590025-XXX
Anschlusskragen Spec.: Brose Norm BN 590011-xxx / BN 590025-xxx



APPLICABLE TIN CONTACTS Einsetzbare verzinnzte Kontakte	
WIRE SIZE Leiterquerschnitt	TE : PN
0.5-1 mm ²	TE: 0-9277771-1
1-2.5 mm ²	TE: 0-927768-1



-2 AS SHOWN
wie gezeichnet

0-1452329-2	PBT-GF15	BLACK	2 POS. SOCKET HOUSING JPT	1
TE PART NR.	MATERIAL	COLOR	DESCRIPTION	ITEM NR.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SHREESHAIL.H 01DEC2011 CHK K.ROTH 01DEC2011 APVD G.MUMPER 01DEC2011		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.3 3 PLC ± 4 PLC ± ANGLES ±° FINISH		NAME 2 POS. SOCKET HOUSING , JPT, LEFT 2-POLIGES BUCHSENGEHAEUSE , JPT, LINKS -	
MATERIAL		PRODUCT SPEC - APPLICATION SPEC 114-18540-1		SIZE A2	CAGE CODE 00779
SEE TABLE		WEIGHT - CUSTOMER DRAWING		DRAWING NO C=1452329	RESTRICTED TO -
				SCALE 2:1	SHEET 1 OF 1