

Coaxial Cable Connector

21_716-50-0-2/003_-

Description

Straight cable jack

Interface standards

IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz

Mechanical Data

Centre contact	soldered
Weight	0.1021 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DOU-00005933
-------------------	--------------

Ordering Information

Single package	21_716-50-0-2/003_-E
Bulk 50 pcs package	21_716-50-0-2/003_-F

Additional Information