



TSSOP-44 to DIP-48 SMT Adapter (0.635 mm pitch, 14 x 6.1 mm body)

REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		6.10				
B		1.50				
C		0.35				
B2		4.00				
C2		7.00				
D		0.285				
D2		1.05				
E		0.635				
F					0.600	
G					0.100	
H					0.025	




(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)