





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-17-005453	14APR2017	QY	CW
	A2	ECR-18-009192	16JUL2018	KW	CW
	B	ECR-20-014876	22OCT2020	WQR	CW
	B1	ECR-21-108894	04AUG2021	WQR	CW

NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: POWDER COATED, GREY
DEGREE OF PROTECTION: IP65 (MATED)

注释:
1. 技术参数:
上壳材料: 铝合金
表面处理: 粉末涂层, 灰色
防护等级: IP65(配合)



SCALE 1:2



T1190242911-000	H24B-TGH/TSH-PG11/PG29	H24B HOOD, TOP ENTRY PG11, SIDE ENTRY PG29, 4 EAR, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 顶出PG11, 侧出PG29, 4耳, 高结构, 灰色粉末喷涂	PG11	PG29
T1190242913-000	H24B-TGH/TSH-PG13.5/PG29	H24B HOOD, TOP ENTRY PG13.5, SIDE ENTRY PG29, 4 EAR, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 顶出PG13.5, 侧出PG29, 4耳, 高结构, 灰色粉末喷涂	PG13.5	PG29
T1190242940-000	H24B-TGH/TSH-M40/PG29	H24B HOOD, TOP ENTRY M40, SIDE ENTRY PG29, 4 EAR, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 顶出M40, 侧出PG29, 4耳, 高结构, 灰色粉末喷涂	M40X1.5	PG29
T1190243240-000	H24B-TGH/TSH-M40/M32	H24B HOOD, TOP ENTRY M40, SIDE ENTRY M32, 4 EAR, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 顶出M40, 侧出M32, 4耳, 高结构, 灰色粉末喷涂	M40X1.5	M32X1.5
T1190244032-000	H24B-TGH/TSH-M32/M40	H24B HOOD, TOP ENTRY M32, SIDE ENTRY M40, 4 EAR, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 顶出M32, 侧出M40, 4耳, 高结构, 灰色粉末喷涂	M32X1.5	M40X1.5
T1190244020-000	H24B-TGH/TSH-M20/M40	H24B HOOD, TOP ENTRY M20, SIDE ENTRY M40, 4 EAR, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 顶出M20, 侧出M40, 4耳, 高结构, 灰色粉末喷涂	M20X1.5	M40X1.5
PART NUMBER 料号	PART DESCRIPTION 描述		PG/M THREAD-1 PG/M 螺纹孔-1	PG/M THREAD-2 PG/M 螺纹孔-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 01JUN2015	TE Connectivity NAME H24B-TGH/TSH-M/PG	
		CHK Chris Wang 01JUN2015		
		APVD Xiang Xu 01JUN2015		
		PRODUCT SPEC 108-137013		
DIMENSIONS: mm		APPLICATION SPEC 114-137013	SIZE A3	
		WEIGHT -	CAGE CODE 00779	DRAWING NO C-T119024XXXX000
MATERIAL -		Customer Drawing	SCALE 1:1	RESTRICTED TO -
			SHEET 1	REV B1