

9001K11J38LGG

Harmony 9001K, illuminated selector switch head, metal, standard handle, green, 30mm, 2 positions, stay put, LED green, 120V



Main

Range of Product	Harmony 9001K
Product or Component Type	Head for illuminated selector switch
Device short name	9001K
Type of operator	maintained
Operator profile	Green standard knob

Complementary

Bezel material	Metal
Mounting diameter	1.18 in (30 mm)
Net Weight	0.54 lb(US) (0.245 kg)
Shape of signaling unit head	Round
Operator position information	2 positions
Contacts type and composition	Without contact block
Mechanical durability	500000 cycles
Light block supply	Direct
Light source	LED
Bulb base	BA 9s
Light block colour	Green
[Us] rated supply voltage	120 V AC/DC
Device presentation	Basic element

Environment

Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Electrical shock protection class	Class II IEC 61140
IP degree of protection	IP66 IEC 60529
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 6
Standards	UL 508 JIS C 852 EN/IEC 60947-5-4 CSA C22.2 No 14 EN/IEC 60947-5-1 JIS C 4520 EN/IEC 60947-1

Product Certifications	NEMA UL 508
Vibration resistance	7 gn 2...500 Hz)IEC 60068-2-6
Shock resistance	50 gn IEC 60068-2-27

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901678526
Nbr. of units in pkg.	1
Package weight(Lbs)	8.80 oz (249.476 g)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.08 in (12.903 cm)
Package 1 width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------