

Within Series Adaptor 33_SMA-50-0-52/199_N

Description

Adaptor plug/jack
SMA plug (male) / SMA jack (female)

For Test & Measurement applications
Quick-screw coupling mechanism, with reduced number of turns

Interface standard
Series SMA - IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz
VSWR	DC - 18 GHz ≤ 1.05 + 0.008 f (GHz)

Mechanical Data

Number of matings	500
Weight	0.0059 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - SMA plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	

Interface - SMA jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00013739
-----------------	--------------

Ordering Information

Single package	33_SMA-50-0-52/199_NE
----------------	-----------------------