

Coaxial Cable Connector
11_BNC-50-4-33/12-_N

Description

Straight cable plug

Interface standards
IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz
Frequency range	DC to 4 GHz
Return loss	23 dB

Mechanical Data

Centre contact	plugged
Outer contact	clamped
Weight	0.0221 kg

Environmental Data

Operating temperature	-60 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze	Nickel Plating
Body	Bronze	Nickel Plating
Other body part	Stainless Steel	
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	Nickel Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00194120
Assembly instruction	DOC-0000294172

Ordering Information

Single package	11_BNC-50-4-33/12-_NE
----------------	-----------------------

Additional Information

Suitable cables	EACON_4C
-----------------	----------