

Within Series Adaptor 34_716-50-0-1/003_-

Description

Bulkhead adaptor jack/jack
7/16 jack (female) / 7/16 jack (female)

Interface standard
Series 7/16 - IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz
VSWR	DC - 4 GHz ≤ 1.02 + 0.05 f (GHz)
Frequency range	4 to 7.5 GHz
Return loss	≥ 20 dB

Mechanical Data

Number of matings	500
Weight	0.2212 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - 7/16 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

Interface - 7/16 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

Related Documents

Catalogue drawing	DCA-00013664
Mounting hole	DOU-00008958

Ordering Information

Single package	34_716-50-0-1/003_-E
----------------	----------------------

Within Series Adaptor

34_716-50-0-1/003_-

Remarks

IP rating unmated: IP 65

IP rating mated: IP 68