



TYPE 1

Single PG/M thread




TYPE 2

Single PG/M thread & without Logo




TYPE 3

Two PG/M threads



TYPE 4


Two PG/M threads & without Logo



REVISIONS				
P	LYN	DESCRIPTION	DATE	BYN
A		INITIAL RELEASE	15JUN2015	GY
B		ECR-20-014403	20MAY2021	BS

TYPE 5


Three PG/M threads



All dimension is same as TYPE 1,except those defined in this TYPE

TYPE 6

Three PG/M threads



All dimension is same as TYPE 1,except those defined in this TYPE

NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: SEE TABLE
DEGREE OF PROTECTION: IP68 (MATED)

注释:
1. 技术参数:
壳体材料: 铝合金
表面处理: 见表格
防护等级: IP68 (配合)

TI1920240325-000	POWDER COATED BLACK	H24BPR-TGH-3M25	M25	M25	M25	-	-	-	-	-	-	-	TYPE 6
TI1920240321-000	POWDER COATED BLACK	H24BPR-TGH-3PG21	-	-	-	PG21	PG21	PG21	-	-	-	-	TYPE 5
TI1920240225-100	POWDER COATED BLACK	H24BPR-TGH-2M25	-	-	-	-	-	-	M25	M25	-	-	TYPE 4
TI1920241232-000	POWDER COATED SILVER WHITE	H24BPR-TGH-2M32	-	-	-	-	-	-	M32	M32	-	-	TYPE 3
TI1920240240-000	POWDER COATED BLACK	H24BPR-TGH-2M40	-	-	-	-	-	-	M40	M40	-	-	TYPE 2
TI1920240140-100	POWDER COATED BLACK	H24BPR-TGH-M40	-	-	-	-	-	-	-	-	M40	-	
TI1920241140-000	POWDER COATED SILVER WHITE	H24BPR-TGH-M40	-	-	-	-	-	-	-	-	M40	-	
TI1920241136-000	POWDER COATED SILVER WHITE	H24BPR-TGH-PG36	-	-	-	-	-	-	-	-	PG36	-	
TI1920241132-000	POWDER COATED SILVER WHITE	H24BPR-TGH-M32	-	-	-	-	-	-	-	-	M32	-	
TI1920241129-000	POWDER COATED SILVER WHITE	H24BPR-TGH-PG29	-	-	-	-	-	-	-	-	PG29	-	
TI1920241125-000	POWDER COATED SILVER WHITE	H24BPR-TGH-M25	-	-	-	-	-	-	-	-	M25	-	
TI1920241121-000	POWDER COATED SILVER WHITE	H24BPR-TGH-PG21	-	-	-	-	-	-	-	-	PG21	-	
TI1920240140-000	POWDER COATED BLACK	H24BPR-TGH-M40	-	-	-	-	-	-	-	-	M40	-	
TI1920240136-000	POWDER COATED BLACK	H24BPR-TGH-PG36	-	-	-	-	-	-	-	-	PG36	-	
TI1920240132-000	POWDER COATED BLACK	H24BPR-TGH-M32	-	-	-	-	-	-	-	-	M32	-	
TI1920240129-000	POWDER COATED BLACK	H24BPR-TGH-PG29	-	-	-	-	-	-	-	-	PG29	-	
TI1920240125-000	POWDER COATED BLACK	H24BPR-TGH-M25	-	-	-	-	-	-	-	-	M25	-	
TI1920240121-000	POWDER COATED BLACK	H24BPR-TGH-PG21	-	-	-	-	-	-	-	-	PG21	-	TYPE 1
PART NUMBER	SURFACE TREATMEN	DESCRIPTION	PG/M THREAD-9	PG/M THREAD-8	PG/M THREAD-7	PG/M THREAD-6	PG/M THREAD-5	PG/M THREAD-4	PG/M THREAD-3	PG/M THREAD-2	PG/M THREAD-1	TYPE	

THIS DRAWING IS A CONTROLLED DOCUMENT.				DATE	15JUN2015
DRAWN				CHK	15JUN2015
DESIGNED				APPROVED	15JUN2015
PRODUCT SPEC				NAME	H24BPR-TGH-PG/M
APPLICATION SPEC				SIZE	108-137014
MATERIAL				SCALE	1:1
FINISH				Customer Drawing	Customer Drawing
WEIGHT				Customer Drawing	Customer Drawing
Customer Drawing				Customer Drawing	Customer Drawing