

Han 3EMV-eg-QB-13,5



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 003 0102
Specification	Han 3EMV-eg-QB-13,5
HARTING eCatalogue	https://b2b.harting.com/09620030102

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® EMC
Type of hood/housing	Screw mounted housing
Description of hood/housing	Straight

Version

Size	3 A
Cable entry	1x Pg 13.5
Locking type	Single locking lever
Field of application	Hoods/Housings for higher EMC requirements
Pack contents	Please order seal screw separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted

Material properties

Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	564b7d75-7bf6-4cfb-acb1-2168eb61b675
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	10
Net weight	57.46 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140072992
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors