



SHELL SIZE	CONTACTS	
	SIZE	PART NO.
6/18	20 PIN	10-195927-206
	20 SOCKET	10-195928-206
20/24	20L PIN	10-195925-206
	20L SOCKET	SEE NOTE 9
6/18	16 PIN	10-247920-168
	16 SOCKET	10-247922-168
20/24	16L PIN	10-247924-167
	16L SOCKET	10-247926-167

ACCESSORIES

(NOT PART OF STANDARD ASSEMBLY)

SEE DRAWING
10-150000

72500-81		REVISIONS		
ZONE	LTR	DESCRIPTION	DATE	APPROVED
A				
B		(CLII) REPLACED 10-497547-06F W/ 10-497547-6FF ECN: A3909	4/25/08	BROOKER



4	1		10-330914-XX1	GASKET	9
3	SEE P/L		SEE CHART	CONTACTS	
2	1		10-101806-()S/850-()S	INSERT, SOCKET	9
			10-101806-()P/850-()P	INSERT, PIN	
1	1		10-150902-XX3	SHELL	9
PART NO.	QTY REQD	CODE IDENT	PART NUMBER	DESCRIPTION	NOTE REF

PARTS LIST			AMPHENOL CORPORATION 40-60 DELAWARE AVE. SIDNEY, NY USA	
UNLESS OTHERWISE SPECIFIED LINEAR DIMENSIONS ARE IN INCHES. TOLERANCES: .XXX ± .010, .XX ± .03, .X ± .1, ANGLES ± 2°. OTHER STANDARDS PER 9-3800 AND MIL-D-1000, NOTE REF			TITLE: CONNECTOR, ELECTRICAL RECEPTACLE, TYPE PT-E()FB, PCB, OLIVE DRAB	
MATERIAL SPEC	PROCESS SPEC TEST 9-3980-1 ASSY 9-3605 9-2437-1 9-2811	SIGNATURES PREPARED WILKINSON CHECKED JOHNSON APPROVED J. Walburn APPROVED [Signature] MATERIAL	DATES 9/18/79 4/16/80 4/16/80 4/17/80	U
SCALE NONE			SIZE CODE IDENT NO. C 77820	71-533245 THRU 71-533259
REF 71-148206/50			SHEET 1 OF 2	TAB.

USE OF THIS DOCUMENT IS UNLIMITED. DOCUMENTS REFERENCED HEREON CONTAIN LIMITED RIGHTS DATA.

NEXT ASSEMBLY

000000001

CN

