




- NOTES:
1. ALL PARTS TO BE BULK PACKED.
 2. CONTACTS ASSEMBLED INTO CONNECTOR. SOLDER CUPS FACING TOP KEYWAY.
 3. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHERE NOTED WITH A TOLERANCE. DIMENSIONS IN BRACKETS [] ARE METRIC.





FACE VIEW
W4282-10SG-300
10-POS.





FACE VIEW
W4282-11SG-300
11-POS.



FACE VIEW
W4282-12SG-300
12-POS.



**RECOMMENDED
PANEL CUTOUT**
STANDARD MULTI-CON-X



PC TAIL VIEW
W4282-10SG-300 - 10-POS. (11&12 CLOSED)
W4282-11SG-300 - 11-POS. (12 CLOSED)
W4282-12SG-300 - 12-POS. (ALL OPEN)

NO. OF CONTACTS

ASS'Y P/N	CONTACTS	HOLE POS. CLOSED
W4282-10SG-300	10 - #20	11, 12
W4282-11SG-300	11 - #20	12
W4282-12SG-300	12 - #20	NONE
W4282-1XSG-300		

CUSTOMER APPROVAL	
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.	
APPROVED BY:	_____
DATE:	_____

A	PAK	09/12/19	DRAWING CREATED AND RELEASED PER DOR 10-2523JS-1		
REV.	INIT.	DATE	DESCRIPTION		
	PAK	10/06/14	ORIG. DRAWN BY:	DATE:	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			CHECKED BY:		
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			APPROVED BY:		
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			SCALE	SIZE	SHEET
▷ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			NTS	B	1 OF 1
			FILE:	DIRECTORY:	PART NUMBER:
			W4282-1XSG-300	SLW	W4282-1XSG-300
					REV A



TITLE: PANEL SOCKET, E-KEY
#20 SOLDER, 12-POS. PATTERN
MULTI-CON-X, WEATHER RESISTANT
STANDARD PRODUCT