


- NOTES:
1. ALL PARTS TO BE BULK PACKED.
 2. CONTACTS ARE INSTALLED INTO CONNECTOR.
 3. ALL DIMENSIONS ARE REFERENCE UNLESS OTHERWISE STATED.
 4. SEE DRAWING HPMISTD FOR HOLE PATTERNS.

ASSY P/N	GROMMET FOR CABLE O.D.
8282-XPG-3DC	DAISY CHAIN
8282-XPG-311	0.09-0.14 [2.3-3.5mm]
8282-XPG-315	0.15-0.17 [3.8-4.3mm]
8282-XPG-318	0.18-0.20 [4.6-5.1mm]
8282-XPG-321	0.21-0.23 [5.3-5.8mm]


KIT P/N	NO. OF CONTACTS
8282-2PG-3XX	(2)-#20
8282-3PG-3XX	(3)-#20
8282-4PG-3XX	(4)-#20
8282-5PG-3XX	(5)-#20
8282-6PG-3XX	(6)-#20
8282-7PG-3XX	(7)-#20
8282-8PG-3XX	(8)-#20
8282-XPG-3XX	

GROMMET SIZE FOR
SINGLE GROMMET OR
"DC" FOR DAISY CHAIN

NO. OF CONTACTS



GROMMET, DAISY CHAIN
FOR 8282-XPG-3DC
MAT'L: RUBBER, BLACK



SHOWN ASSEMBLED KIT
FOR CUSTOMER REFERENCE ONLY

CUSTOMER APPROVAL	
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.	
APPROVED BY: _____	
DATE: _____	

DIMENSIONS IN BRACKET [] ARE METRIC.

RoHS COMPLIANT

B	JD	10-13-17	UPDATED CONNECTOR AND PIN HEIGHT PER ECR 9020	
A	AN	11-03-11	DRAWING CREATED PER DOR 11-E149SL	
REV.	INIT.	DATE	DESCRIPTION	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: AN	DATE: 11-01-11
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			CHECKED BY:	
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			APPROVED BY:	
= CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			SCALE NTS	SIZE B
			SHEET 1 OF 1	
			FILE: 8282-XPG-3XX	DIRECTORY: SLW
			PART NUMBER: 8282-XPG-3XX	REV B

conxall
601 E. WILDWOOD VILLA PARK, IL 60181

TITLE: CABLE TO CABLE CONN. ASS'Y
(2-8) #20 PIN CONTACTS, SOLDER
MINI-CON-X
CUSTOMER: STANDARD PRODUCT