






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
AD	00		L	REVISED PER ECO-15-008006	17NOV2015	NK

D



- 1 THIS COVER IS TO BE USED IN PAIRS, WITH A DOUBLE ROW HOUSING. NUMBER OF POSITIONS INDICATED PERTAINS TO THE HOUSING.
- 2 THESE VIEWS APPLY TO -1 AND -2 ONLY.

C



B

OBSOLETE	91.44	[3.600]	88.90	[3.500]	35	72	3-102396-4	
OBSOLETE	88.90	[3.500]	86.36	[3.400]	34	70	3-102396-3	
OBSOLETE	86.36	[3.400]	83.82	[3.300]	33	68	3-102396-2	
OBSOLETE	83.82	[3.300]	81.28	[3.200]	32	66	3-102396-1	
	81.28	[3.200]	78.74	[3.100]	31	64	3-102396-0	
OBSOLETE	78.74	[3.100]	76.20	[3.000]	30	62	2-102396-9	
	76.20	[3.000]	73.66	[2.900]	29	60	2-102396-8	
OBSOLETE	73.66	[2.900]	71.12	[2.800]	28	58	2-102396-7	
OBSOLETE	71.12	[2.800]	68.58	[2.700]	27	56	2-102396-6	
OBSOLETE	68.58	[2.700]	66.04	[2.600]	26	54	2-102396-5	
OBSOLETE	66.04	[2.600]	63.50	[2.500]	25	52	2-102396-4	
	63.50	[2.500]	60.96	[2.400]	24	50	2-102396-3	
OBSOLETE	60.96	[2.400]	58.42	[2.300]	23	48	2-102396-2	
OBSOLETE	58.42	[2.300]	55.88	[2.200]	22	46	2-102396-1	
OBSOLETE	55.88	[2.200]	53.34	[2.100]	21	44	2-102396-0	
OBSOLETE	53.34	[2.100]	50.80	[2.000]	20	42	1-102396-9	
	50.80	[2.000]	48.26	[1.900]	19	40	1-102396-8	
OBSOLETE	48.26	[1.900]	45.72	[1.800]	18	38	1-102396-7	
OBSOLETE	45.72	[1.800]	43.18	[1.700]	17	36	1-102396-6	
	43.18	[1.700]	40.64	[1.600]	16	34	1-102396-5	
	40.64	[1.600]	38.10	[1.500]	15	32	1-102396-4	
	38.10	[1.500]	35.56	[1.400]	14	30	1-102396-3	
	35.56	[1.400]	33.02	[1.300]	13	28	1-102396-2	
	33.02	[1.300]	30.48	[1.200]	12	26	1-102396-1	
	30.48	[1.200]	27.94	[1.100]	11	24	1-102396-0	
	27.94	[1.100]	25.40	[1.000]	10	22	102396-9	
	25.40	[1.000]	22.86	[.900]	9	20	102396-8	
	22.86	[.900]	20.32	[.800]	8	18	102396-7	
	20.32	[.800]	17.78	[.700]	7	16	102396-6	
	17.78	[.700]	15.24	[.600]	6	14	102396-5	
	15.24	[.600]	12.70	[.500]	5	12	102396-4	
	12.70	[.500]	10.16	[.400]	4	10	102396-3	
	10.16	[.400]	7.62	[.300]	3	8	102396-2	
	7.62	[.300]	5.08	[.200]	2	6	102396-1	
C			B		A		REF ¹ NO OF POSN	PART NUMBER
COVER DIMENSIONS								

102396

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.13[.005]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-

FINISH

-

MATERIAL

FLAME RETARDANT THERMOPLASTIC, COLOR - BLACK

DWN
E. BRANDBERG
CHK
J. HERRINGTON
APVD
J. HERRINGTON

13SEP94
13SEP94
13SEP94

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

COVER
MASS TERMINATION AMPMODU
2.54[.100] CL

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=102396

RESTRICTED TO
-

SCALE
5:1

SHEET
1 of 1

REV
L