

Coaxial Panel Connector 22_MMBX-50-0-1/111_N

Description

Straight bulkhead receptacle jack

Interface standards
SUHNER-MMBX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	12.4 GHz

Mechanical Data

Chassis torque	2 Nm
Number of matings	100
Weight	0.0014 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	LCP (Liquid crystal polymer)	

Related Documents

Outline drawing	DOU-00010456
Catalogue drawing	DCA-00010458

Ordering Information

Single package	22_MMBX-50-0-1/111_NE
----------------	-----------------------