


LOC	DIST	REVISIONS			
G	86	P	LTR	DESCRIPTION	DATE
		R		ECR-13-000998	09FEB2013
					PK
					HS



1 TIN PL .000150 MIN THK
PER ASTM B 545

2 PART NO: 324461; .071 LB.
PART NO: 1-324461-0; .071 LB.
PART NO: 2-324461-2; .082 LB.
PART NO: 2-324461-3; .082 LB.

3 CLEANED, UNPLATED

4 PRELIMINARY - NOT FOR PRODUCTION
.045 MAX BURR ALLOWED INSIDE THE WIRE
BARREL ID IN AREA OF SIGHT HOLE.

5

.72	.97	1.89	190,000- 231,000	1	COPPER	2-324461-3
				2	ASTM-B-75	2-324461-2
.72	.72	1.65	CM	3	ANNEALED	1-324461-0
				4		324461
"C"	"B"	"A"	WIRE RANGE	FINISH	MATERIAL	PART No

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 4/24/89	TE Connectivity	
DIMENSIONS: INCHES		CHK MS FEHER 4/24/89	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD WJ VOCKROTH 11/8/89	SPLICE, BUTT, AMPOWER WIRE SIZE: 4/0 AWG	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -	SIZE A3	
MATERIAL SEE TABLE		APPLICATION SPEC -	CAGE CODE 00779	DRAWING NO C=324461
FINISH SEE TABLE		WEIGHT 2	RESTRICTED TO -	SCALE 2:1
		CUSTOMER DRAWING	SHEET 1 OF 1	REV R