

DESCRIPTION: M8 // M // 3P // PANEL MOUNT SOLDER CUP


SPECIFICATIONS:

MATERIALS:
HOUSING: PBT, UL94 V-0, BLACK
CONTACTS: GOLD PLATED BRASS (SEE P/N KEY BELOW)
NUT & WASHER: (SEE P/N KEY BELOW)
SHELL: (SEE P/N KEY BELOW)
ORING: EPDM, BLACK

ELECTRICAL:
RATED CURRENT: 3A
RATED VOLTAGE: 60V
INSULATION RESISTANCE: 100 MOhms MIN.
CONTACT RESISTANCE: 10 mOhms MAX.

ENVIRONMENT:
OPERATING TEMPERATURE: -40°C TO +85°C
WATER PROOF: IP67

MAX WIRE AWG: 24
MAX TORQUE: 1.25 in-lbs





NOTE:
NUT AND WASHER INTENDED TO BE
INSTALLED OUTSIDE PANEL. CAN OMIT
WASHER TO INCREASE PANEL THICKNESS

3 = BRASS/NICKEL SHELL & NUT & WASHER
S = 316 STAINLESS STEEL SHELL & NUT & WASHER

855-003-10YR00Y

1 = GOLD FLASH
4 = 10μ" GOLD



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:
03/04/2016

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS
SHEET 1 OF 1
REV 5
DWG NO. 855-003-103R00Y