



DESCRIPTION: M5 MALE - PANEL MOUNT (REAR) - VERTICAL - 2 POSITION



NOTE:

MATERIAL

HOUSING: PBT UL94V-0, BLACK
CONTACT: BRASS
NUT: BRASS
SHELL: BRASS
O-RING: NBR, BLACK

FINISH

CONTACT: GOLD PLATED
OVER 50 μ NICKEL
NUT: NICKEL PLATED
SHELL: NICKEL PLATED

ELECTRICAL


RATED CURRENT: 1A
RATED VOLTAGE: 60V
INSULATION RESISTANCE: 100 M Ω hms MIN.
CONTACT RESISTANCE: 10 m Ω hms MAX.
WATER PROOF: IP67

ENVIRONMENT


OPERATION TEMPERATURE: -40°C TO +85°C

852-002-113R00Y


1 = GOLD FLASH
4 = 10 μ " GOLD




NUT



RECOMMEND PANEL CUT-OUT
MAX. PANEL THICKNESS: 0.063" [1.60]



RECOMMENDED PCB
LAYOUT



RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-03-16

NorComp

SCALE:

NTS

SHEET

OF

1

1

REV

7

DWG NO.

852-002-113R00Y