



COPALUM Lite Sealed Terminals and Splices

Rugged, Sealed Terminals made from Aluminum at up to 60% Less Weight

LIGHTWEIGHT

- 60% weight savings vs. copper terminals
- 53% weight savings vs. drop-forged aluminum terminals

QUALIFIED

- Full qualification for use in commercial aircraft

EFFICIENT

- Single-step crimp for conductor termination and watertight wire sealing
- Grease-free COPALUM dry crimp technology
- Crimp die sets are compatible with existing crimp heads and power units

FLEXIBLE DESIGN

- Easy wire insertion with ample room for conductors
- Available with single or dual-hole terminals
- Compatible with a variety of cable constructions

Lightweight Terminations for Aerospace Applications

COPALUM Lite sealed terminals and splices from TE Connectivity (TE) feature the time-tested dry crimp technology that has provided 30 years of reliable connectivity to the commercial aerospace industry. The new optimized design provides a weight reduction of up to 60% over copper and drop-forged lugs.

Efficient, Reliable Terminations

The terminal's perforated insert in the crimp barrel penetrates aluminum oxides on the conductor to form a long-lasting, oxide-free termination. The single crimp process also eliminates the need for a second crimp for wire sealing. Weight savings originate from the lightweight aluminum alloy, optimized wall thickness, and short barrel length.

TE Components . . . TE Technology . . . TE Know-how . . .

AMP | AGASTAT | CII | HARTMAN | KILOVAC | MICRODOT | NANONICS | POLAMCO | Raychem | Rochester | DEUTSCH
SEACON Phoenix | LL Rowe | Phoenix Optix | AFP | SEACON

Get your product to market faster with a smarter, better solution.

COPALUM Lite Sealed Terminals and Splices

Rugged, Sealed Terminals Made from Aluminum
At Up To 60% Less Weight



Single-Hole Lug



Dual-Hole Lug



Butt Splice

Electrical		Mechanical	Part No.		
Wire Size (AWG)	Current (A)	Crimp Tensile Strength, Min	Dual-Hole Lug	Single Hole Lug	Butt Splice
2	152	375 lb (1668 N)	2102579-1	2102571-1	2226081-1
1/0	202	675 lb (3003 N)	2102580-1	2102572-1	2226082-1
2/0	235	825 lb (3670 N)	2102581-1	2102573-1	2226083-1
3/0	275	975 lb (4337 N)	2102582-1	2102574-1	2226084-1
4/0	303	1125 lb (5004 N)	2102583-1	2102575-1	2226085-1

Part numbers are for straight terminals and splices. Consult TE for custom configurations.

APPLICATIONS

- Commercial Aircraft
- Unmanned Aerial Vehicles
- Primary Power Feeders
- Grounding Systems

MATERIALS

- **Base Material:** Aluminum
- **Finish:** Tin over nickel plating

PHYSICAL PROPERTIES


- **Temperature Rating:** 175°C
- **Sealed Crimp:** 80 psi
- **Salt Spray:** 500 hours

STANDARDS AND TEST REPORT

- **Product Specification:** 108-32088
- **Application Specification:** 114-32098
- **Qualification Test Report:** 501-134033
- **Application Tooling Instruction Sheet:** 408-32087

CABLE COMPATIBILITY

- BMS 13-60
- BMS 13-78
- ABS0949 (AD)
- ASNE0438 (YV)
- MIL-SPEC



te.com/copalumlite

© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved.

1-1773853-6 02/17

AMP, AGASTAT, CII, COPALUM, DEUTSCH, HARTMAN, KILOVAC, LL Rowe, MICRODOT, NANONICS, POLAMCO, Raychem, SEACON, TE, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies.

Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

Consult TE for the latest dimensions and design specifications.

North America +1 800 522 6752 • Asia Pacific +86 0 400 820 6015 • France +33 1 34 20 86 86 • Germany +49 6251 133 1999 • United Kingdom +44 800 267 666
Visit te.com for additional country contacts.