

1		2		3		4		5		6		7		8	
△B MSAS-XXBMMB-SL7001 XX: No. Of Pin				REV.	ECN NO.		DATE		SIGN		DESCRIPTION				
				B	C210561		2021/04/15		Vicky		△B X4				
Connector Clamp Ring O-Ring Clamp Cage Seal Sealing Nut M12*1.0 55.0(Ref.) ∅20.1 16.0 Hex. 16.0 Hex.															
3P 4P 5P 8P Pin Assignments Front View UNIT:mm TOLERANCE .X±0.25 .XX±0.1 .XXX±0.05 ANGLES±1° △B TITLE N SEN, M12 A -SHLD, SCREW CABLE W/O SR, M, M, FI SCREW IN △B SCALE I:1 SIZE A4 SHEET 1 OF 1 REV. B WC-REV. A.5 QC:Inspection item Amphenol LTW 安費諾亮泰企業股份有限公司 ITEM NO DWG NO CUSTOMER ALTW DRAWN BY Mila CHECKED BY Cary APPROVED BY Jerry DATE 2015-09-28 DATE 2015-09-28 DATE 2015-09-28 Note: * RoHS Compliant * QC Important Dimension * Waterproof rate: IPX7, mated * Connector Housing: Thermoplastic, Black Pin: Copper alloy, Gold plated Extension Nut: Metal Nut: Metal O-Ring: Rubber, Gray * Clamp Ring: Metal * O-Ring: Rubber, Gray * Clamp Cage: Thermoplastic, Black * Sealing Nut: Metal * Seal: Rubber, Gray, OD:∅4.0mm~∅7.5mm * One set unassembled in one pe bag															
8 W10814-03-0001A2															