


REV	ECRN	DATE
1	NEW PRODUCTION	20190403




NO	CUSTOMER`S ITEM	LENGTH	TOLERANCE	SUPPLIER`S ITEM
1		152MM	±5MM	9.00ACCA2484.00AR
2		305MM	±10MM	9.00ACCA2484.00BR

PIN WIRING

1 ——— 1

NOTES:
1.ELECTRICALTEST:100%OPEN,SHORT&MIS WIRE TEST.
2.CONTACT RESISTANCE:10 ohm,
3.INSULATOR RESISTANCE:5M ohm.
4.HIGH VOLTAGE:DC 300V 0.01sec.
5.MUST BE ROHS COMPLIANT.

⑧					
⑦					
⑥					
⑤		TIE	WHITE TIE L=70mm	5	PCS
④	J.000008.0500R	TIN WIRE	TIN WIRE OD:0.8MM	5	G
③		MOLDING	PVC 45P Red, , white, green, black, , yellow	10	G
②		TERMINAL	Banana head Ø 3.0 mm phosphor copper nickel plated	10	PCS
①	A.000X07.0302R	CABLE	UL 2733 16AWG*1C PVC 60P jacket : Red, , white, green, black, , yellow OD=3.0±0.15mm L=LENGTH	5	PCS
NO.	PART NO	ITEM	DESCRIPTION	Q`TY	UNIT

RoHS COMPLIANT				朋联电子有限公司 DongGuan PengLian Electronics Co.,Ltd TEL:076938835098/38835095 FAX:076938835091			
				比例: FREE TITLE: Banana terminal wire			
DRAWN BY	袁小政	20190403	單位: mm	SUPPLIER`S ITEM: 9.00ACCA2484.00XR			
CHECKED BY				CUSTOMER:			
APPROVED BY				CUSTOMER`S ITEM:			
				DRAWING NO. ACCA-2484		DATE	2019.04.03