

SUMMARY

Wires

Low voltage	4
-------------	---

Image is for illustrative purpose only

Series	SP	Download
Termination type	Female solder	Request a quote
IP rating	50	Catalog
AWG wire size	28.00 - 20.00	
Cable Ø	4.00 - 5.20 mm	
Status	active	
Matching parts	SAP.M04.GLA.5NZ	

TECHNICAL DETAILS

Mechanics

Shell Style/Model	*:
Keying	3 keys (alpha=0, gamma=60, plug: male contacts, receptacle: female contacts)
Housing Material	Proprietary sulfone, gray
Variant	NZ : Black collet nut for bend relief

Performance

Configuration	SP.M04 : 4 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated Current	11.5 Amps

Specifications

Contact Type:	Solder
Contact Dia.:	1.3 mm (0.0512in)
Bucket Dia.:	1.1 mm (0.04in)
Min. Conductor:	0.36 mm ² (AWG 22)
Max. Conductor:	1 mm ² (AWG 18)
Test voltage (kV rms)	Contact-contact: 1.60
Air clearance min.:	0.95 mm
Creepage distance min.:	0.95 mm

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Others

Endurance (Shell): >2000 mating cycles
Temp (min / max): -50°C / +170°C

DRAWINGS



RECOMMENDED BY LEMO

Tools

Cables

CMN.04.T22.047QGC	TPR	Grey	
CMN.04.T22.048QGZE	TPR (medical)	Grey	
140240	PVC	Black	
140250	PVC	Grey	

40140	PVC	Black	
40260	PVC	Black	
4080	PVC	Grey	
4221	PVC	Black	
4280	PVC	Black	
80080	PVC	Grey	
80082	PVC	Red	
80084	PVC	Black	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.