

							Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, 37 poles, male, straight, with solder pins 3.7, and screw locks.	Maßstab/ Scale 1.5:1	
						Detail.	05/03/02	CV				
						Insp.						
						Stand.						
09 65 421 6703	4-40 UNC	2										
09 65 421 7703	4-40 UNC	3					HARTING EURL F-95972 Paris				TB 09 65 421 x70x	Blatt/ Page 3
09 65 421 5703	4-40 UNC	0,76 µm Au	29723	05/03/02	CV							
Part number	S.l. thread	Performance level	Mod.	Dat.	Name					Sub.		

09 65 421 6703
D-Sub - S PCB connector

Other applications

gender	male connector, straight
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	37 way
Board fixing	without grounding board locks
flange	with screw lock UNC 4-40
Performance level	Performance level 2
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 65 421 5703
D-Sub - S PCB connector

Other applications

gender	male connector, straight
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	37 way
Board fixing	without grounding board locks
flange	with screw lock UNC 4-40
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



Data sheets are available in following formats
2D files

Typenblatt

Typenblatt

09 65 421 7703
D-Sub - S PCB connector

Other applications

gender	male connector, straight
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	37 way
Board fixing	without grounding board locks
flange	with screw lock UNC 4-40
Performance level	Performance level 3
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF