

Coaxial Panel Connector 27_BNC-50-0-1/133_N

Description

Right angle bulkhead receptacle jack

Interface standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Number of matings	500
Weight	0.0158 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPALATE (R) Plating
Body	Brass	SUCOPALATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPALATE (R) Plating
Washer	Bronze	SUCOPALATE (R) Plating

Related Documents

Outline drawing	DOU-00010300
Catalogue drawing	DPA-00035601
Mounting hole	DOU-00008762

Ordering Information

Single package	27_BNC-50-0-1/133_NE
----------------	----------------------