



REVISIONS						
P	F	ZONE	LTR	DESCRIPTION	DATE	DWN
0			F	REVISED PER ECO-15-008006	17NOV2015	NK



1. NO. OF POS. PERTAINS TO HOUSING SIZE.
2. THIS COVER TO BE USED WITH 102536.
③ OBSOLETE PART NUMBER

3.600	3.500	35	72	3-102681-1
3.500	3.400	34	70	3-102681-2
3.400	3.300	33	68	2-102681-3
3.300	3.200	32	66	2-102681-4
3.200	3.100	31	64	2-102681-5
3.100	3.000	30	62	2-102681-6
3.000	2.900	29	60	2-102681-7
2.900	2.800	28	58	2-102681-8
2.800	2.700	27	56	2-102681-9
2.700	2.600	26	54	2-102681-10
2.600	2.500	25	52	2-102681-11
2.500	2.400	24	50	2-102681-12
2.400	2.300	23	48	1-102681-13
2.300	2.200	22	46	1-102681-14
2.200	2.100	21	44	1-102681-15
2.100	2.000	20	42	1-102681-16
2.000	1.900	19	40	1-102681-17
1.900	1.800	18	38	1-102681-18
1.800	1.700	17	36	1-102681-19
1.700	1.600	16	34	1-102681-20
1.600	1.500	15	32	1-102681-21
1.500	1.400	14	30	1-102681-22
1.400	1.300	13	28	1-102681-23
1.300	1.200	12	26	1-102681-24
1.200	1.100	11	24	1-102681-25
1.100	1.000	10	22	1-102681-26
1.000	.900	9	20	1-102681-27
.900	.800	8	18	1-102681-28
.800	.700	7	16	1-102681-29
.700	.600	6	14	1-102681-30
.600	.500	5	12	102681-1
C	B	A	NO. OF POS.	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.005 ANGLES	CONTRACT NO DB 10-31-80 CHK APPD APPD DSGN APPD OTHER APPD	TE TE Connectivity NAME COVER-HALF, LATCH, MASS TERMINATION, AMPMODU, .100 &, FULL BAR POLARIZATION SIZE CODE IDENT NO DRAWING NO C 00779 102681 SCALE SHEET 1 OF 1
--	--	---