

Product data sheet

Characteristics

9001KYK117

Control station, harmony 9001K, 10A, zinc, red, 1 push button 1NO + 1NC STOP-BREAK GLASS, NEMA 3/4/13



Main

Range of Product	Harmony 9001K
Product or Component Type	Complete control station
Device short name	KY 9001KY
Provided equipment	Contact block Legend plate
Contact block name	KA1

Complementary

Enclosure/cubicle description	Surface mounting
Enclosure material	Die cast zinc alloy Red
Type of Installation	Indoor/outdoor
Control station composition	1 push-button 1 NO + 1 NC STOP-BREAK GLASS
Connections - terminals	Screw-clamp terminals
[Ie] rated operational current AC	10 A

Environment

NEMA degree of protection	NEMA 3/4/13
---------------------------	-------------

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901039846
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.70 in (32.258 cm)
Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	32.26 in (81.935 cm)
Package 1 Weight	3.25 lb(US) (1.474 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------