

**Series 80 Mighty Mouse
Backshells and Accessories**
809S060, 809A060 and 809B060 Shrink Boots



Lipped straight shrink boots-Type 1 high performance elastomer

- -75° C to +165° C
- Excellent resistance to fuels, oils, solvents and heat.

Fully recovered boot shown. As supplied part will vary.



Boot Size	Shell Size			Part Number Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive
	Series 800, 801, 802, 803, 804	Series 805	Series 811	
1	5/6	8	5	809S060-1
2	7	9	6,7	809S060-2
3	8, 9	10, 11	8,9	809S060-3
4	10, 11, 12, 13	12, 15	N/A	809S060-4
5	14, 15, 16, 17	18, 19	N/A	809S060-5
6	19, 21	23	N/A	809S060-6

Lipped straight shrink boots- Type 2 zero halogen

- Low Smoke, Zero Halogen
- Meets U.S. and E.U. toxicity requirements.

Fully recovered boot shown. As supplied part will vary.



Boot Size	Shell Size			Part Number Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive
	Series 800, 801, 802, 803, 804	Series 805	Series 811	
1	5/6	8	5	809S060-1H
2	7	9	6,7	809S060-2H
3	8, 9	10, 11	8,9	809S060-3H
4	10, 11, 12, 13	12, 15	N/A	809S060-4H
5	14, 15, 16, 17	18, 19	N/A	809S060-5H
6	19, 21	23	N/A	809S060-6H

Lipped 90° right angle shrink boots- Type 1 high performance elastomer

- -75° C to +165° C
- Excellent resistance to fuels, oils, solvents and heat.

Fully recovered boot shown. As supplied part will vary.



Boot Size	Shell Size			Part Number Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive
	Series 800, 801, 802, 803, 804	Series 805	Series 811	
1	5/6	8	5	809A060-1
2	7	9	6,7	809A060-2
3	8, 9	10, 11	8,9	809A060-3
4	10, 11, 12, 13	12, 15	N/A	809A060-4
5	14, 15, 16, 17	18, 19	N/A	809A060-5
6	19, 21	23	N/A	809A060-6

Lipped 90° right angle shrink boots- Type 2 zero halogen

- Low Smoke, Zero Halogen
- Meets U.S. and E.U. toxicity requirements.

Fully recovered boot shown. As supplied part will vary.



Boot Size	Shell Size			Part Number Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive
	Series 800, 801, 802, 803, 804	Series 805	Series 811	
1	5/6	8	5	809A060-1H
2	7	9	6,7	809A060-2H
3	8, 9	10, 11	8,9	809A060-3H
4	10, 11, 12, 13	12, 15	N/A	809A060-4H
5	14, 15, 16, 17	18, 19	N/A	809A060-5H
6	19, 21	23	N/A	809A060-6H

Lipped 45° angle shrink boots- Type 1 high performance elastomer

- -75° C to +165° C
- Excellent resistance to fuels, oils, solvents and heat.

Fully recovered boot shown. As supplied part will vary.



Boot Size	Shell Size		Part Number Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive
	Series 800, 801, 802, 803, 804	Series 805	
1	5/6	8	809B060-1
2	7	9	809B060-2
3	8, 9	10, 11	809B060-3
4	10, 11, 12, 13	12, 15	809B060-4
5	14, 15, 16, 17	18, 19	809B060-5
6	19, 21	23	809B060-6

Dimensions in Inches (millimeters) are subject to change without notice.