

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISION PER EG00-2081-00 (TEXT TO ENGLISH TRANSLATED)	06-SEP-00	R.S	G.F
	C3	ECO-19-003069	01OCT2019	RS	DR


STRIP FORM ON MIDDLE REEL (CARDBOARD REEL, DIA. ABOUT 450mm)

BANDWARE AUF MITTELSPULE (PAPPSPULE, Ø CA. 450mm)




ORDER NO. BESTELL-NR.	CROSS SECTION QUERSCHNITT		STRIP LENGTH ABISOLIER-LÄNGE /mm $\triangle 2$	TYPE AUSFÜHRUNG	COLOUR FARBE	L ₁ /mm	L ₂ /mm	d ₁ /mm	s ₁ /mm	d ₂ /mm	COLOUR TYPE FARBREIHE	PACKING UNIT VERPACKUNGSEINHEIT PARTS/STÜCK REEL/SPULE
	mm ²	AWG $\triangle 1$										
966 900-2	0.50	20	10	NORMAL NORMAL	WHITE WEIß	14 ±1.5	8 ±0.4	1.0 ^{+0.14}	0.15 ±0.05	2.8 ±0.2	DIN/1	10000

NOMINAL SIZE NENNGRÖßE /mm	R /mm
0.25/0.34	2.7
0.5 - 0.75	3.6
1 - 1.5	4.2
2.5	5.0



- $\triangle 1$ THE AWG CROSS-SECTION CAN SLIGHT DEVIATING OF THE DIN-STANDARD CROSS-SECTION VALUES
- $\triangle 2$ RECOMMENDED STRIP LENGTH
- $\triangle 3$ MAX. INSULATION-DIA. OF WIRE: d₂ MIN.- 0.1
- $\triangle 4$ COLOUR TYPE 1: COLOUR PER TELEMECANIQUE STANDARD
COLOUR TYPE 2: COLOUR PER WEIDMÜLLER STANDARD
DIN COLOUR TYPE: COLOUR PER DIN 46228 PART 4
- $\triangle 5$ TUBULAR END-SLEEVE WITH PLASTIC SLEEVE ACCORDING TO DIN 46228 PART 4
- $\triangle 6$ LENGTH "L1" INCLUDES MOLDING FLASH PRESENT IN THIS ZONE

- $\triangle 1$ DER AWG-QUERSCHNITT KANN VON DEN DIN-NORM QUERSCHNITTSWERTEN GERINGFÜGIG ABWEICHEN.
- $\triangle 2$ EMPFOHLENE ABISOLIERLÄNGE
- $\triangle 3$ MAX. ISOLATIONS-Ø DER LEITUNG: d₂ MIN.- 0.1
- $\triangle 4$ FARBREIHE 1: FARBEN NACH TELEMECANIQUE STANDARD
FARBREIHE 2: FARBEN NACH WEIDMÜLLER STANDARD
DIN: FARBEN NACH DIN 46228 TEIL 4
- $\triangle 5$ ADERENDHÜLSE MIT KUNSTSTOFFHÜLSE NACH DIN 46228 TEIL 4



TOLERANCES UNLESS OTHERWISE SPECIFIED:
 n. ISO 8015
 n. ISO 2768 - mH -E
 n. DIN 16901 - 140

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. WERNER 29-APR-96		
		CHK R.SCHMIDT 29-APR-96		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD G.FELDMEIER 12-SEP-00	NAME TUBULAR END-SLEEVE WITH PLASTIC SLEEVE, STRIP FORM, MIDDLE REEL ADERENDHÜLSE MIT KUNSTSTOFFHÜLSE, BANDWARE, MITTELSPULE	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC -	DRAWING NO A300779 ©-966900	
MATERIAL PP/E-Cu	FINISH Sn (SEE TABLE)	APPLICATION SPEC -	RESTRICTED TO -	
		WEIGHT -	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	SCALE -	SHEET 1 of 1
				REV C3