

## Han 10 A FLANSCHGUMMIDICHTUNG



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 09 20 000 9992                                                                        |
| Specification      | Han 10 A FLANSCHGUMMIDICHTUNG                                                         |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09200009992">https://b2b.harting.com/09200009992</a> |

### Identification

|                          |                    |
|--------------------------|--------------------|
| Category                 | Accessories        |
| Series of hoods/housings | Han A <sup>®</sup> |
| Type of accessory        | Flange gasket      |

### Version

|      |      |
|------|------|
| Size | 10 A |
|------|------|

### Material properties

|                             |               |
|-----------------------------|---------------|
| Material (seal)             | NBR           |
| Colour (seal)               | Black         |
| RoHS                        | compliant     |
| ELV status                  | compliant     |
| China RoHS                  | e             |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances  | Not contained |
| REACH SVHC substances       | Not contained |

### Commercial data

|                                |               |
|--------------------------------|---------------|
| Packaging size                 | 10            |
| Net weight                     | 0.01 g        |
| Country of origin              | Germany       |
| European customs tariff number | 40169300      |
| GTIN                           | 5713140038295 |



**Pushing Performance**  
Since 1945

Commercial data

|        |                                      |
|--------|--------------------------------------|
| ETIM   | EC002943                             |
| eCl@ss | 27440291 Connector component (parts) |