



Pushing Performance  
Since 1945

# Han 34 HPR - carrier hood 2xM40



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 40 134 0623  |
| Specification      | Han 34 HPR - carrier hood 2xM40   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19401340623">https://b2b.harting.com/19401340623</a> |

## Identification

|                             |                  |
|-----------------------------|------------------|
| Category                    | Hoods/Housings   |
| Series of hoods/housings    | Han® HPR EasyCon |
| Type of hood/housing        | Carrier hood     |
| Description of hood/housing | Angled           |

## Version

|                      |   |
|----------------------|---|
| Size                 | 34 HPR  |
| Cable entry          | 2x M40  |
| Locking type         | Screw locking                                 |
| Field of application | Hoods/housings for harsh outdoor environments |

## Technical characteristics

|  |  |
|--|--|
| Tightening torque (screw locking)      | 4 Nm   |
| Tightening torque                      | 6 Nm Protection cover<br>1.5 Nm Inserts        |
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65<br>IP68<br>IP69 / IPX9K acc. to ISO 20653 |

## Material properties

|                         |   |
|-------------------------|---|
| Material (hood/housing) | Aluminium die-cast<br>Corrosion resistant |
|-------------------------|---|



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                            |
|--------------------------------------|----------------------------|
| Surface (hood/housing)               | Powder-coated              |
| Colour (hood/housing)                | RAL 9005 (jet black)       |
| Material (seal)                      | EPDM                       |
| Material (locking)                   | Stainless steel            |
| RoHS                                 | compliant                  |
| ELV status                           | compliant                  |
| China RoHS                           | e                          |
| REACH Annex XVII substances          | Not contained              |
| REACH ANNEX XIV substances           | Not contained              |
| REACH SVHC substances                | Not contained              |
| California Proposition 65 substances | Yes                        |
| California Proposition 65 substances | Nickel<br>Naphthalene      |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08)       |
| Requirement set with Hazard Levels   | R1 (HL 1-3)<br>R7 (HL 1-3) |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 1,150 g                                  |
| Country of origin              | China                                    |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140175426                            |
| ETIM                           | EC000437                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |