

Han-Snap Latching part w. strain relief



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 000 9990
Specification	Han-Snap Latching part w. strain relief
HARTING eCatalogue	https://b2b.harting.com/09330009990

Identification

Category	Accessories
Series	Han-Snap®
Type of accessory	Latching parts
Description of the accessory	With strain relief and panel mounting parts

Version

Pack contents	1 latching part with strain relief 1 panel mounting part
---------------	---

Technical characteristics

Tightening torque	0.8 Nm
Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP20
Retention force	200 N Without guiding 300 N With guiding

Material properties

Material (accessories)	Polycarbonate (PC)
Colour (accessories)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60068-2-6 Vibration (sinusoidal)
	IEC 60068-2-27 Shock

Commercial data

Packaging size	10
Net weight	20.7 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140050679
ETIM	EC002939
eCl@ss	27440392 Connector (accessories)