





CONNECTOR	CATALOG MODULE #	QTY	SIZE NO.	CONTACT QTY	MATING PIN	MAX. CURRENT (PER CONTACT)	CONTACT SPACING	VOLTAGE RATING
SOCKET	FP0105	4	8	4	1.25 X 7.00 [.049 X .276]	35 amps	7.50 [.2953]	250
	FP0315	1	22	6	.64 [.025] SQ.	3 amps	2.50 [.0984]	125 VOLTS
	FP0500	1	LEFT MOUNTING FLANGE					
	FP0501	1	RIGHT MOUNTING FLANGE					



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 26 JAN 2006 R. GRZYBOWSKI		tyco Electronics		Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK 26 JAN 2006 P. DAMATO		NAME	
		APVD 26 JAN 2006 S. FLICKINGER		PRODUCT SPEC		SOCKET CONNECTOR, FLATPAQ, RIGHT ANGLE, SOLDER TAILS	
		APPLICATION SPEC		-		-	
		WEIGHT		-		-	
		FINISH		-		-	
MATERIAL		-		SIZE		CAGE CODE	
-		-		DRAWING NO		RESTRICTED	
-		-		A200779		C=6648043	
-		-		CUSTOMER DRAWING		SCALE 3:1	
-		-		SHEET 2 OF 2		REV A	