




	NO FLAT	1410465-9
	315°	1410465-8
	270°	1410465-7
	225°	1410465-6
	180°	1410465-5
	135°	1410465-4
	90°	1410465-3
	45°	1410465-2
	0°	1410465-1
FINISH	A°	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR THE CUSTOMER'S INFORMATION IT IS NOT TO BE REPRODUCED OR COPIED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF TYCO ELECTRONICS						DWN TREAA 24APR2009		Tyco Electronics		Harrisburg, PA 17105-3608	
DIMENSIONS:						TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		KEYING/GUIDE RECEPTEALC, VITA 41	
mm								PRODUCT SPEC		-	
						0 PLC ±.010 1 PLC ±.010 2 PLC ±.010 3 PLC ±.010 4 PLC ±.010 ANGLES ±.010		APPLICATION SPEC		-	
MATERIAL						FINISH		SIZE CAGE CODE DRAWING NO		RESTRICTED TO	
-						-		A 00779 C = I410465		-	
WEIGHT						-		SCALE		5:1 SHEET 1 OF 1 REV B	
CUSTOMER DRAWING											