

Han-Eco Cable gland M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 000 5111
Specification	Han-Eco Cable gland M20
HARTING eCatalogue	https://b2b.harting.com/19410005111

Identification

Category	Accessories
Series of hoods/housings	Han-Eco®
Type of accessory	Cable gland

Technical characteristics

Tightening torque	4 Nm Fitting 3 Nm Cap nut
Wrench size	24
Limiting temperature	-40 ... +125 °C
Size	M20
Clamping range	6 ... 13 mm

Material properties

Material (cable glands)	Polyamide (PA)
Colour (cable gland)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel



Pushing Performance
Since 1945

Material properties

Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Commercial data

Packaging size	2
Net weight	6 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140192997
ETIM	EC000441
eCl@ss	27140801 Screwed cable gland (electrical)