

Pneum. contact metal OD4mm F+valve ang.



Image is for illustration purposes only. Please refer to product description.

Identification

| | |
|----------------------------|-------------------------|
| Category | Contacts |
| Type of contact | Pneumatic contact |
| Description of the contact | With shut-off Angled |

Version

| | |
|-----------------------|-----------------|
| Gender | Female |
| Manufacturing process | Turned contacts |

Technical characteristics

| | |
|----------------------|----------------|
| Limiting temperature | -20 ... +85 °C |
| Operating pressure | ≤10 bar |
| Tube outer diameter | 4 mm |

Material properties

| | |
|-----------------------------|---------------------|
| Material (contacts) | Brass |
| Material (seal) | HNBR (hydrated NBR) |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |

Material properties

| | |
|--------------------------------------|-------------|
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead |
| | Nickel |
| | Naphthalene |

Specifications and approvals

| | |
|----------|--|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |
|----------|--|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 10 |
| Net weight | 16 g |
| Country of origin | Romania |
| European customs tariff number | 85366990 |
| GTIN | 5713140189256 |
| ETIM | EC000796 |
| eCl@ss | 27440204 Contact for industrial connectors |