

## Han-Yellock M-c 0.75mm<sup>2</sup> (Au)



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 11 05 000 6123                                                                        |
| Specification      | Han-Yellock M-c 0.75mm <sup>2</sup> (Au)                                              |
| HARTING eCatalogue | <a href="https://b2b.harting.com/11050006123">https://b2b.harting.com/11050006123</a> |

### Identification

|                 |               |
|-----------------|---------------|
| Category        | Contacts      |
| Series          | Han-Yellock®  |
| Type of contact | Crimp contact |

### Version

|                       |                 |
|-----------------------|-----------------|
| Gender                | Male            |
| Manufacturing process | Turned contacts |

### Technical characteristics

|                         |                      |
|-------------------------|----------------------|
| Conductor cross-section | 0.75 mm <sup>2</sup> |
| Conductor cross-section | AWG 18               |
| Rated current           | ≤20 A                |
| Contact resistance      | ≤2 mΩ                |
| Stripping length        | 6.5 mm               |

### Material properties

|                             |                                                        |
|-----------------------------|--------------------------------------------------------|
| Material (contacts)         | Copper alloy                                           |
| Surface (contacts)          | Gold plated                                            |
| RoHS                        | compliant with exemption                               |
| RoHS exemptions             | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                  | compliant with exemption                               |
| China RoHS                  | 50                                                     |
| REACH Annex XVII substances | Not contained                                          |



Pushing Performance  
Since 1945

Material properties

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| REACH ANNEX XIV substances           | Not contained                        |
| REACH SVHC substances                | Yes                                  |
| REACH SVHC substances                | Lead                                 |
| ECHA SCIP number                     | b51e5b97-eeb5-438b-8538-f1771d43c17d |
| California Proposition 65 substances | Yes                                  |
| California Proposition 65 substances | Lead<br>Nickel                       |

Specifications and approvals

|                |                          |
|----------------|--------------------------|
| Specifications | IEC 60664-1<br>IEC 61984 |
|----------------|--------------------------|

Commercial data

|                                |                                            |
|--------------------------------|--------------------------------------------|
| Packaging size                 | 100                                        |
| Net weight                     | 0.68 g                                     |
| Country of origin              | Germany                                    |
| European customs tariff number | 85366990                                   |
| GTIN                           | 5713140109421                              |
| ETIM                           | EC000796                                   |
| eCl@ss                         | 27440204 Contact for industrial connectors |