

SUMMARY

Wires

| | |
|-------------|----|
| Low voltage | 14 |
|-------------|----|



Image is for illustrative purpose only

| | |
|------------------|-----------------------------------|
| Series | 2B |
| Termination type | Male solder |
| IP rating | 50 |
| AWG wire size | 30.00 - 22.00 |
| Cable Ø | 0.00 - 0.00 mm |
| Status | active |
| Matching parts | FGJ.2B.314.CLLD52 |

Download

[Request a quote](#)
[Eplan](#)
[Catalog](#)

TECHNICAL DETAILS

Mechanics

| | |
|-------------------|---|
| Shell Style/Model | EC*: Fixed receptacle with two nuts (back panel mounting) |
| Keying | 2 keys (alpha=37.5, plug: female contacts, receptacle: male contacts) |
| Housing Material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Weight | 15.22 g |

Performance

| | |
|---------------|---------------------------|
| Configuration | 2B.314 : 14 Low Voltage |
| Insulator | L: PEEK (UL 94 / V-0/1.5) |
| Rated Current | 6.5 Amps |

Specifications



| | |
|--------------------------|-------------------------------|
| Contact Type: | Solder |
| Contact Dia.: | 0.7 mm (0.028in) |
| Bucket Dia.: | 0.8 mm (0.031in) |
| Max. Stranded Conductor: | 0.34 mm ² (AWG 22) |
| Max. Conductor: | 0.34 mm ² (AWG 22) |
| R (max): | 6.1 mOhm |
| Vtest (contact-shell): | 1350 V (AC), 1910 V (DC) |
| Vtest (contact-contact): | 1150 V (AC), 1630 V (DC) |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Others

Endurance (Shell): 5000
Temp (min / max): -55°C / +250°C
Humidity (max): <=95% [at 60 deg C /140 F]
Vibration: 15 g [10 Hz - 2000 Hz]
Shock Resistance: 100 g [6 ms]
Climatical Category: 50/175/21
Shielding (min): 75 dB (10 MHz)
Shielding (min): 40 dB (1 GHz)
Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

| | A | B | E | L | M | N | S1 | S3 | e |
|-----|------|------|------|------|------|------|------|------|---------|
| mm. | 20 | 19.2 | 6.5 | 26.7 | 3.5 | 24.6 | 13.5 | 17 | M15x1.0 |
| in. | 0,79 | 0,76 | 0,26 | 1,05 | 0,14 | 0,97 | 0,53 | 0,67 | |




RECOMMENDED BY LEMO

Tools

Spanner 2: [DCH.91.201.PA](#)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

| | | | |
|--------------------|---------------|-------|--|
| CMN.14.T22.068PGCE | PVC | GREY |  |
| CMN.14.T22.068PGZE | | Grey |  |
| CMN.14.T22.068PNCE | PVC | Black |  |
| CMN.14.T22.068PNZE | | |  |
| CMN.14.T28.056PGZE | | Grey |  |
| CMN.14.T28.056PNZE | | |  |
| CMN.14.T28.056QGZE | TPR (medical) | Grey |  |
| 114260 | PTFE | White |  |
| 214140 | PVC | Black |  |
| 214240 | PTFE | White |  |
| 314250 | PVC | Grey |  |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.