


Für diese Unterlage behalten wir uns alle Rechte vor, auch für den Fall der Patentverletzung oder Gebrauchsmusterverletzung. Sie darf ohne unsere vorherige schriftliche Zustimmung weder vervielfältigt noch sonstwie benutzt, noch Dritten zugänglich gemacht werden.

Nur rot gestempelte oder auf Laufkarte gedruckte Dokumente unterliegen dem Änderungsdienst und sind zur Fertigung freigegeben. Only red stamped or on jobcard printed documents are managed. These documents are approved for production.


All Rights reserved, including possible patents or trademarks. Documents shall not be provided to a third party or duplicated in any form without prior written permission.

CAD: Pro/ENGINEER


Additional coding
View in direction B




K1CWBM-P07WBC0-0000
Mechanical coding: B
Color coding: red





K1CWCm-P07WBC0-0000
Mechanical coding: C
Color coding: blue




K1CWDm-P07WBC0-0000
Mechanical coding: D
Color coding: green



K1CWAM-P07WBC0-0000
Mechanical coding: A
Color coding: light brown



Only insert
View in direction A
10:1



Technical information

- Max. cable Ø5.0mm (Based on cable with one braided shield)
- Solder contacts: AWG28
- Current load: 1A@Δt40° (Single contact)
- Test voltage: 750V (acc. SAE AS 13441:1998, Contact to contact)
- Rated voltage: 250V (acc. SAE AS 13441:1998) 2)

All shown connectors are according to DIN EN 61984:2009 connectors without breaking capacity (COC)!

1) For crimp information, torque, etc. see assembly instruction 010.650.001.000.002 (www.odu.de/downloads)

2) Maximal operating voltage at sea level up to 2.000 m. Rated voltage applies no other electrical safety standard. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. This must be evaluated in the frame of equipment engineering.

				General tolerances to DIN ISO 2768-mK		PE-modell-nr.:	
				Toleration to DIN ISO 8015		CAD-nr.:	sheet.:
				2014	date	name	00058435
				prep.	13.11.	Unterblüm.	scale:
				app.			6:1
				norm.			
				 <i>A perfect alliance.</i>		drawing nr.:	copy
						K1CW.M-P07WBC0-0000	
index	notice	date	name			replacement for:	nr.

