







LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
GP	00		A1	REVISED PER ECO-09-025699	11-DEC-2009	KK	AEG	
			A2	REVISED PER ECO-12-010437	28SEP2012	CJV	DLG	
			B	REVISED PER ECO-15-018557	30DEC2015	TX	SH	

- 1 MATERIAL: LCP, BLACK.
- 2 MATERIAL: PHOSPHOR BRONZE PER ASTM B 103.
- 3 FINISH: 0.76µm MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03µm MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81µm MIN NICKEL PLATE PER QQ-N-290.
- 4 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- 5 WITH KAPTON PLACEMENT DOT INSTALLED.
- 6 PACKAGED IN TUBES.
- 7 PACKAGED IN TAPE AND REEL.
- 8 CONNECTOR PIN IDENTIFIERS: SYMETRICAL VERTICAL CONNECTORS CAN BE APPLIED TO BOARD IN EITHER ORIENTATION.
- 9 FINISH: 0.38µm MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03µm MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81µm MIN NICKEL PLATE PER QQ-N-290.
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



1888020-3 & -7
SCALE 5:1


1888020-4 & -8, 1-1888020-0
SCALE 5:1



1888020-1 & -5
SCALE 5:1

1888020-2 & -6
SCALE 5:1

OBSOLETE	9	7	-	-	-	-	-	-	-	1888020-6	5	1888020-8
		7	-	-	-	-	-	-	-	1888020-5	5	1888020-7
		6	36	16	17.4	8	36	15.8	36	-		1888020-6
6		26	12	13.4	6	26	11.8	26	-		1888020-5	
OBSOLETE	3	7	-	-	-	-	-	-	-	1888020-2	5	1-1888020-0
		7	-	-	-	-	-	-	-	1888020-2	5	1888020-4
		7	-	-	-	-	-	-	-	1888020-1	5	1888020-3
		6	36	16	17.4	8	36	15.8	36	-		1888020-2
6		26	12	13.4	6	26	11.8	26	-		1888020-1	
OBSOLETE	0	FINISH	PACKAGING	N	E	D	C	B	A	POSN	MADE FROM	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009.		DWN M.E. COWHER 01JUL05 CHK R.R. HENRY 01JUL05 APVD R.R. HENRY 01JUL05	TE Connectivity	
DIMENSIONS: mm		NAME	EVERCLEAR Mini-SAS VERTICAL RECEPTACLE CONNECTOR ASSEMBLY, SURFACE MOUNT	
		PRODUCT SPEC 108-2234 APPLICATION SPEC	SIZE CAGE CODE DRAWING NO A100779C=1888020	
MATERIAL SEE NOTES		WEIGHT -		
FINISH SEE TABLE		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 2
			REV B	

