

Han-Yellock 10 cover f. housing w/o seal



Image is for illustration purposes only. Please refer to product description.

Part number	11 20 003 5407
Specification	Han-Yellock 10 cover f. housing w/o seal
HARTING eCatalogue	https://b2b.harting.com/11200035407

Identification

Category	Accessories
Series of hoods/housings	Han-Yellock®
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings Thermoplastic

Version

Size	Han-Yellock® 10
------	-----------------

Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	10
Net weight	12.52 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140110694
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors