

Han TC200 Buchsenkontakt 35mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 6221
Specification	Han TC200 Buchsenkontakt 35mm ²
HARTING eCatalogue	https://b2b.harting.com/09110006221

Identification

Category	Contacts
Series	TC 200
Type of contact	Crimp contact

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	35 mm ²
Rated current	≤200 A
Contact resistance	≤0.3 mΩ
Stripping length	20 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	2
Net weight	26.92 g
Country of origin	Germany
European customs tariff number	85359000
GTIN	5713140015326
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors