

## DisplayPort to HDMI 4K Active Adapter Video Converter, DP ver 1.2, HDCP 1.3, DPCP 1.0 (M/F), 4K 30 Hz

MODEL NUMBER: **P136-000-UHD-V2**



### Highlights

- Active adapter for use with any Displayport port
- Connect a 4K HDMI monitor to a computer with a Displayport 1.2 output
- Displayport Male to HDMI Female
- HDCP 1.3 and DPCP 1.0 compliant

### Package Includes

- P136-000-UHD-V2 DisplayPort 1.2 to HDMI 4K Active Converter Adapter

### Description

This P136-000-UHD-V2 DisplayPort 1.2 to HDMI 4K Active Converter Adapter allows you to connect a computer with a DisplayPort output to an HDMI monitor. Supports computer video resolutions up to 4K x 2K at 24/30 Hz (Ultra HD). It is an active adapter, converting both Single-Mode and Dual-Mode (DP++) DisplayPort output. It's perfect for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals. Adapter is plug-and-play and requires no drivers or other software. Backwards compatible with previous DisplayPort versions (1.0, 1.1, 1.2). Fully molded ends ensure long life enjoyment.

### Features

- Supports DisplayPort 1.2a input and HDMI1.4b output
- Active adapter for use with any Displayport port, converts Single-Mode and Dual-Mode (DP++) DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals
- Supports HDMI highest video resolution 4K x 2K @ 24/30 Hz
- Content protection of HDCP Rx and Tx keys to support HDCP repeater
- Supports up to 8 channel LPCM, compressed audio(AC-3,DTS) and HBR audio format
- Supports up to 192khz audio frame rate and up to 24-bit audio sample size
- Integrated both HDCP Rx and Tx keys to support HDCP repeater
- HDCP 1.3 and DPCP 1.0 compliant
- Powered from DisplayPort source
- Plug and Play

## Specifications

OVERVIEW	
UPC Code	037332188328



Powering Business Worldwide



Product Type	Video Adapter
Technology	HDMI; DisplayPort
<b>CONNECTIONS</b>	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / in.)	5.90 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	14.99 x 9.91 x 1.27
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	1.3
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.