

UIC558-HTE-13PIN-PG21



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series	HARTING UIC
Identification	558
Type of hood/housing	Hood

Version

Number of contacts	13
Version	Top entry
Cable entry	1x Pg 21
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-50 ... +125 °C
Degree of protection acc. to IEC 60529	IP69 / IPX9K acc. to ISO 20653 mated condition

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	Black
Material (seal)	Silicone
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UIC 50558 IRS 50558 IEC 61373 Category 2 IEC 60529
----------------	---

Commercial data

Packaging size	1
Net weight	114 g
Country of origin	India
European customs tariff number	85389099
GTIN	5713140183902
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors