



SURFACE/OBERFLAECHE									
STYLE:		COAT THICKNESS 2.5 UNTIL 4 µm Sn OVER 1.3 UNTIL 2.2 µm Ni							
Ausfuehrung Sn:		Schichtdicke 2.5 bis 4 µm Sn ueber 1.3 bis 2.2 µm Ni							
CABLE DIRECTION LEFT AND RIGHT Kabelabgang links und rechts	-	-	-	-	-	-	-	-	-
	3-1355154-1	B	B	2	18	PIN CONTACT/Stiftkontakt	TIN/Zinn	CuFe2	2-1355350-1
				1	1	PIN HEADER/Stiftwanne	NATURAL/Natur	PET-GF30	
	2-1355154-1	B	B	2	18	PIN CONTACT/Stiftkontakt	TIN/Zinn	CuFe2	2-1355350-1
				1	1	PIN HEADER/Stiftwanne	NATURAL/Natur	PET-GF30	
	1-1355154-1	B	A	2	18	PIN CONTACT/Stiftkontakt	TIN/Zinn	CuFe2	1-1355350-1
				1	1	PIN HEADER/Stiftwanne	BLACK/schwarz	PET-GF30	1355348-1
TE ORDER NO. BESETELL-NR.		REV. REV.	CODE. KOD.	POS. POS.	QTY. STK.	DESCRIPTION BENENNUNG	SURFACE/COLOR FARBE OBERFLAECHE	MATERIAL Material	SUITABLE FOR: SHIELD dazu passend: Abdeckkappe TE
									USED WITH: SOCKET HOUSING DAZU GEHOEHRT: Buchsengehaeuse TE



- NOTES:
Bemerkungen:
- MATERIAL MARKING
Materialkennzeichnung
 - WARPAGE -0.3MM PERMITTED
Verzug -0.3mm zulaessig
 - PACKAGING: IN TRAY NO. 740966-1
Verpackung: in Produkttraeger 740966-1
 - PRODUCT SPECIFICATION: 108-18030
Produktspezifikation: 108-18030
 - PRESS OUT FORCE > 25N
SOLDERABILITY ACC. TO DIN IEC 68 Part 2-20
Ausdruckkraft > 25N
Loetbarkeit gemass DIN IEC 68 Teil 2-20, Alterung 3
 - CAVITY MARKING
Nestkennzeichnung
 - TE PN FOR HOUSING
TE Teile Nr. fuer Gehaeuse
 - TE PN FOR ASSY
TE Teile Nr. fuer Assembly
 - REVISION (HOUSING)
Aenderungssstand (Gehaeuse)
 - OTHER CODINGS UPON REQUEST
weitere Kodierungen auf Anfrage

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN O.Frank	24 JUN 1999	TE Connectivity	
DIMENSIONS:		CHK B.Fieberling	24 JUN 1999	NAME	
mm		APVD	-	PRODUCT SPEC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		SIZE	
0 PLC ±0.2		1 PLC ±0.2		CAGE CODE	
2 PLC ±0.2		3 PLC ±0.2		DRAWING NO	
4 PLC ±0.2		5 PLC ±0.2		RESTRICTED TO	
ANGLES		WEIGHT		A1	
MATERIAL		ca. 6g		00779	
SEE TABLE		SEE TABLE		C=1355154	
siehe Tabelle		siehe Tabelle		CUSTOMER DRAWING	
		SCALE		2:1	
		SHEET		1 OF 1	
		REV		B4	